

Ultra Light-Weld® OP-4-20632-H High T_g Light Path Adhesive for Fiber Optical Assembly

APPLICATIONS

- Fiber Optic Couplings and Prisms

FEATURES & BENEFITS

- Low-Shrinkage UV Cure (<0.2%) with High Optical Clarity 300-1,800 nm
- High-Strength Bonds Resist Yellowing

OTHER FEATURES

- Good Thermal Cycling with Minimal Degradation of Optics or Strength
- High Glass-Transition Temperature (T_g)

Dymax high-performance optical adhesives cure upon exposure to UV/Visible light in seconds and are designed to increase productivity, lower assembly costs, and enhance worker safety. When cured with Dymax light-curing spot lamps, focused-beam lamps, or flood lamps, they deliver optimum speed and performance for optical assembly. This product is in full compliance with the RoHS Directives 2002/95/EC and 2003/11/EC.

Ultra Light-Weld® OP-4-20632-H is a clear, UV/Visible light-curable adhesive designed for durable bonding of fiber optic couplings. OP-4-20632-H was designed for maximum resistance to yellowing and maintains its dimensions when thermally cycled. OP-4-20632-H has high bond strength to optical glass and most metals. Although the product fully cures in seconds upon UV or visible light exposure, heating the UV-cured product to 150°C for 1 hour will increase the T_g to 100°C and may further improve bond strength.

TYPICAL UNCURED PROPERTIES (not specifications)

Solvent Content	None-100% Reactive Solids	
Composition	Acrylate	
Appearance	Optically Clear	
Solubility	Alcohols/Ketones/Chlorinated Solvents	
Flash Point	Over 93°C (>200°F)	
Refractive Index, n _D ²⁰	1.522	ASTM D-1218
Viscosity, (Brookfield, 25°C, 20 rpm)	500 cP	ASTM D-2556

TYPICAL CURED PROPERTIES (not specifications)

Linear Shrinkage, after UV cure	0.2%	ASTM D-2566
Refractive Index, n _D ²⁰	1.554	ASTM D-1218
Glass Transition, T _g	100°C (UV cure and heat)	ASTM E-831
Glass Transition, T _g	50°C (UV cure without heat)	ASTM E-831
CTE α ₁ (Below T _g)	45 x 10 ⁻⁶ in/in/°C	ASTM E-831
CTE α ₂ (Above T _g)	110 x 10 ⁻⁶ in/in/°C	ASTM E-831
CTE (-50°C to 200°C)	91 x 10 ⁻⁶ in/in/°C	ASTM E-831
Durometer Hardness	D75	ASTM D-2240
Tensile at Break	8,900 psi	ASTM D-638
Modulus of Elasticity	800,000 psi	ASTM D-638
Elongation at Break	2%	ASTM D-638
Tensile Compression Shear, Glass-to-Glass	2,200 psi (exceeds glass strength)	DSTM D-250*
Thermal Range (Brittle/Degrades)	-55° to +200°C (-65 to 400°F)	DSTM D-200*
24 hr Water Absorption	1.0 %	ASTM D-570
2 hr Boiling Water Absorption	1.2%	ASTM D-570

*DSTM Refers to Dymax Standard Test Method



© 2006-2011 Dymax Corporation. All rights reserved. All trademarks in this guide, except where noted, are the property of, or used under license by Dymax Corporation, U.S.A.

Technical data provided is of a general nature and is based on laboratory test conditions. Dymax does not warrant the data contained in this bulletin. Any warranty applicable to the product, its application and use is strictly limited to that contained in Dymax standard Conditions of Sale. Dymax does not assume responsibility for test or performance results obtained by users. It is the user's responsibility to determine the suitability for the product application and purposes and the suitability for use in the user's intended manufacturing apparatus and methods. The user should adopt such precautions and use guidelines as may be reasonably advisable or necessary for the protection of property and persons. Nothing in this communication shall act as a representation that the product use or application will not infringe on a patent owned by someone other than Dymax or act as a grant of license under any Dymax Corporation Patent. Dymax recommends that each user adequately test its proposed use and application before actual repetitive use, using the data in this communication as a general guideline.

Technical Data Collection Prior to 2006

Rev. 03/16/2011

Dymax Corporation
860.482.1010
info@dymax.com
www.dymax.com

Dymax Oligomers & Coatings
860.626.7006
oligomers&coatings@dymax.com
www.dymax-oc.com

Dymax Europe GmbH
+49 (0) 611.962.7900
info_de@dymax.com
www.dymax.de

Dymax UV Adhesives & Equipment (Shenzhen) Co Ltd
+86.755.83485759
dymaxasia@dymax.com
www.dymax.com.cn


Dymax UV Adhesives & Equipment (Shanghai) Co Ltd
+86.21.37285759
dymaxasia@dymax.com
www.dymax.com.cn

Dymax Asia (H.K.) Limited
+852.2460.7038
dymaxasia@dymax.com
www.dymax.com.cn

Dymax Korea LLC
82.2.784.3434
info@dymax.kr
www.dymax.co.kr

CURE DATA

Lamp	Dymax® 2000-EC	Dymax® 5000-EC	Dymax® Bond Box	Dymax® BlueWave® 50	ADAC™ 50
Light Type Lamp Type	UV/Visible 8" x 8" Flood	UV/Visible 5" x 5" Flood	UV/Visible 8" Rotating Stage	UV/Visible 3/16" Spot	UV/Visible 3/16" Spot
Maximum Lamp Intensity @ 365 nm Intensity @ Time of Test @ 365 nm	50 mW/cm ² 20 mW/cm ²	300 mW/cm ² 150 mW/cm ²	150 mW/cm ² 50 mW/cm ²	4,000 mW/cm ² 2,500 mW/cm ²	4,000 mW/cm ² 2,500 mW/cm ²
Adhesive Absorption Range (nm) Equipment Output Range (nm)	300-400 300-500	300-400 300-500	300-400 300-500	300-400 300-500	300-400 300-500
Typical Cure Speed (Seconds) Fixture Between Glass Slides Tack-Free Surface Cure 1/16-Inch Bead	1 1 3	1 1 3	1 1 3	1 1 3	1 1 3


STORAGE & SHELF LIFE

Store material in a cool, dark place when not in use. Do not expose to UV light or sunlight. Material may polymerize upon prolonged exposure to ambient light. This material has a minimum 12-month shelf life from date of shipment, unless otherwise specified, when stored between 10°C [50°F] and 32°C [90°F] in the original, unopened container.

DISPENSING THE MATERIAL

This material may be dispensed with a variety of manual and automatic applicators or other equipment as required. Questions relating to dispensing and curing systems for specific applications should be referred to Dymax Application Engineering.

SAFETY

Wear impervious gloves and/or barrier cream. Repeated or continuous skin contact with liquid adhesive will cause irritation and should be avoided. Do not wear absorbent gloves. Remove adhesive from skin with soap and water. Never use solvents to remove adhesive from skin or eyes.

CAUTION

For industrial use only. Avoid breathing vapors. Avoid contact with eyes and clothing. In case of contact, immediately flush with water for at least 15 minutes; for eyes, get medical attention. Wash clothing before reuse. Keep out of reach of children. Do not take internally. If swallowed, vomiting should be induced at once and a physician called. For specific information, refer to the Material Safety Data Sheet before use.